

Food & Beverage Processing Cleaners

EW 2000

Alkaline Egg Wash Solution

Core 3: Personal Attention Every customer requires special attention and has their own demands put on them. Our staff will design and implement a program designed to fit your needs.

Core 3: Experience With our full staff of formulators, chemists, & marketing professionals we have been bringing cutting edge products to market for over 70 years.

Core 3:Technology Through daily contact with industry professionals, we are continuously updating and improving our products to make sure you perform at your best.

Synthetic Labs offers industry-leading solutions for businesses and professionals who demand exceptional results.

EW-2000

UN1760



EW 2000 Alkaline Egg Wash Solution

What is EW 2000?

A heavy duty alkaline cleaner for use in automatic egg washing machines. Eliminates the waste and performance-control problems typically experienced when using egg wash powders. Regular maintenance of the cleaning solution will drastically improve performance.

Benefits:

- Incredible non foaming formula.
- Highly concentrated for economical dilutions.
- Cleans and removes build up in one shot.
- Highly alkaline for long economical dilutions.

Instructions:

For institutional or commercial use.

Maintain a concentration of 0.25 to 1.0 oz per gallon of water in wash tank as necessary to maintain a minimum pH of 10.5. The use dilution required depends on the degree of soil and amount of egg breakage in the machine. Maintain wash water at a temperature that is at least 20°F higher than the egg itself, but not less than of 90°F. Do not use wash water containing greater than 2 ppm of iron. Follow washing with an approved sanitizing rinse. The temperature of the sanitizing rinse should be equal to or higher than that of the wash solution. Pack eggs only after they are reasonably dry.

Do not use on aluminum, galvanized, or precious metal surfaces.

Rinse thoroughly with potable water. Allow surface to air dry. Tilt movable surfaces to assist water runoff.

Do not use concentrate on aluminum, tin or zinc-plated surfaces. Pitting or surface deterioration may result.

Tech Specs:

Available Packages	
2891-275	275 Gallon Tote
2891-55	55 Gallon Plastic Drum
2891-30	30 Gallon Plastic Drum
2891-15	15 Gallon Plastic Drum
2891-5.25	2x2.5 Gallon Jugs
2891-5	5 Gallon Plastic Pail
2891-4	4 Gallon Case



Toll Free: 800-255-4050 24 Victory Lane, Dracut, MA 01826 www.syntecpro.com